



Smart Output

de producto:

SMART OUTPUT

USD Precio:

Contacto Hach

Disponible

Water engineers and technicians will find McCrometer has a versatile Smart Output mag meter solution that is Sensus or Itron system compatible for nearly every type of AMR and AMI application. These accurate, reliable and cost-effective mag meters are available for line sizes from 4 to 138 inches in hot tap insertion or full bore styles, which can be AC or DC powered, battery powered or solar. Smart Output gives water utility managers the flexibility they need to network the flow meters across their distribution systems with the AMI solution of their choice. Smart Output reduces costs, calls, travel, and labor, while it increases efficiency, ensuring your data is accurate.

Smart Output mag meters from McCrometer are designed with a highly intelligent module in their transmitters that is similar to a communication protocol. This capability allows McCrometer mag meters to transmit data on a schedule or on demand, as well as receive diagnostic queries to ensure or update meter operation. There's no need for technicians to gather flow data manually or check meter status with McCrometer's Smart Output mag meters.

With advanced plug-and-play, real-time Smart Output communications, McCrometer's FPI Mag Flow Meter, SPI Mag Flow Meter and Ultra Mag Flow Meter provide highly effective solutions for automatic meter reading (AMR) and advanced meter infrastructure (AMI) in support of utility smart grids that help conserve valuable water resources, reduce expensive non-revenue water costs, and simplify daily operations and routine maintenance.

McCrometer's Smart Output technology is backed by the company's 60-plus years of solving flow measurement problems.

Especificaciones

Exactitud:	±0,5%
Opciones de energía:	AC/DC, Battery, or Solar
Requisitos de instalación:	Requisito: apenas 1 diámetro aguas arriba
Tamaño lineal:	4" - 138"